

# Wilks Enterprise Inc.

140 Water Street, South Norwalk, CT 06854 · Tel 203-855-9136 Fax 203-838-9868

Visit our Web Site – [www.wilksir.com](http://www.wilksir.com)

## InfraCal® TOG/TPH Analyzer & Accessory Price List

InfraCal Analyzer Models	
405-1009	<b>InfraCal IR Platform Analyzer, Model HATR-T2</b> Complete with HATR-T2 Stainless Steel Trough Sample Stage with built-in Cubic Zirconia ATR Crystal, Power Supply and Instruction Manual. <i>Note: P/N 405-1009 is a direct replacement for and supercedes P/N 405-0009, which is only available on a special order basis. Contact Wilks Enterprise for further details and pricing.</i>
405-0003	<b>InfraCal 10mm Cuvette Holder Analyzer, Model CVH</b> Complete with CVH Sample Stage for 10mm Quartz Cuvettes, Power Supply and Instruction Manual (does not include 10mm quartz cuvette cells)
405-0014	<b>InfraCal 1mm Cuvette Holder Analyzer, Model CVH-1</b> Complete with CVH-1 Sample Stage for 1mm Quartz Cuvettes, Power Supply, Instruction Manual (does not include 10mm quartz cuvette cells)
405-0010	<b>InfraCal Cylindrical Cell Holder Analyzer, Model CVH-50</b> Complete with CVH-50 Sample Stage with mounted 50mm Cylindrical Quartz Cell, Power Supply and Instruction Manual.
405-0002	<b>InfraCal Card Reader Analyzer, Model CH.</b> Complete with CH Sample Stage for use with InfraCal reusable IR Sample Plates with Sapphire Window, Power Supply and Instruction Manual. (Does not include InfraCal Reusable IR Sample Plates).
Sample Handling Accessories	
401-1009	<b>Replacement Stainless Steel Trough Sample Stage</b> with built-in Cubic Zirconia ATR Crystal for use with Model HATR-T2. <i>Note: P/N: 401-1009 is a direct replacement for and supercedes P/N 403-0011, which is only available on a special order basis. Contact Wilks Enterprise for further details and pricing.</i>
403-0012	<b>Set of Four 10mm Quartz Cuvette Cells</b> with Teflon Stopper for use with Model CVH.
403-0027	<b>Set of Four 1mm Quartz Cuvette Cells</b> with Teflon Stopper for use with Model CVH-1.
403-0020	<b>Replacement Mounted Type 34 50mm Cylindrical Quartz Cell</b> with Teflon Stopper for use with Model CVH-50.
403-0010/5	<b>InfraCal Reusable IR Sample Plates</b> with Sapphire Window, pkg. 5
Accessories	
403-0018	<b>InfraLog Serial Printer</b> Prints calibration and measurement data, complete with sequence number, date and time. Includes all required cables. Interfaces directly with InfraCal serial numbers 010410 and higher. NOTE: InfraCal serial numbers lower than 010410 will require a factory upgrade of the firmware to accommodate this printer. This upgrade will enable the user to create and modify calibration tables from the InfraCal's built-in keypad. <b>The cost of this upgrade is \$225.00</b>
403-0013	<b>Carrying Case for InfraCal Analyzers</b> with pre-diced pluck foam. 18.5" x 14.6" x 8"; 8 lbs.
403-0003	<b>External 12v Battery Pack</b> with 120v/60Hz charger (for use in North America). Includes carrying case with shoulder strap and cigarette lighter adapter cable for connection to analyzer. Provides 16 hours of continuous operation.
403-0002	<b>Cigarette Lighter Adapter Cable</b>

*Applying Infrared Technology to the Real World*

<b>Computer Software</b>	
<b>403-0016/32</b>	<b>InfraWin Windows Based Software for InfraCal Analyzers</b> , ver. 1.02 Software specifically designed for InfraCal users that require PC control capability, data logging, multiple calibration tables and numerical and graphic reporting on CD-Rom. <b>ENGLISH VERSION WINDOWS ONLY.</b>
<b>Conversion Kits</b>	
<b>401-1008</b>	<b>IR Platform HATR-T2 Stainless Steel Trough Sample Stage</b> with built-in Cubic Zirconia ATR Crystal, Pre-Amp and Detector converts Models HATR-T, CVH, CVH-1 and CH to Model HATR-T2.
<b>401-0003</b>	<b>10mm Cuvette Holder CVH Sample Stage</b> for use with 10mm Quartz Cuvette Cells, converts Model HATR-T2 to Model CVH (includes P/N 402-1002 Pre-Amp Board Assembly). <b>Note: Must be ordered at the same time with Model HATR-T2</b>
<b>401-1011</b>	<b>10mm Cuvette Holder CVH Sample Stage</b> for use with 10mm Quartz Cuvette Cells, converts Models CH, CVH-1, HATR-T and HATR-T2 to Model CVH (includes P/N 402-1002 Pre-Amp Board Assembly and P/N 313-0001 Detector).
<b>401-0010</b>	<b>Cylindrical Cell Holder CVH-50 Sample Stage</b> with mounted 50mm Cylindrical Quartz Cell, converts Models CVH, CVH-1, CH, HATR-T and HATR-T2 to Model CVH-50. Includes Sample Stage with mounted cell, source, firmware and labor. <b>Note: Analyzer must be returned to the factory for this conversion.</b>
<b>NOTE: Conversion Kits for other InfraCal TOG/TPH Analyzer Models are available on special request. Contact Wilks Enterprise Inc for details.</b>	
<b>403-0001</b>	<b>Universal Switching Power Supply and Line Cord</b> for use with InfraCal Analyzers. 90-264 VAC, 50 – 60Hz input, regulated 12v/25 watt output.
<b>403-0014</b>	<b>Replacement Source/Cable Assembly</b> for Models CVH, CVH-1, CH, HATR-T and HATR-T2
<b>403-0026</b>	<b>Replacement Source/Cable Assembly</b> for Model CVH-50.
<b>403-0005</b>	<b>Dust Cover</b>
<b>100-2001</b>	<b>InfraCal TOG/TPH User's Manual – Model HATR-T2 &amp; CH</b>
<b>100-2002</b>	<b>InfraCal TOG/TPH User's Manual – Model CVH &amp; CVH-50</b>
	<b>On-Site Training</b> Wilks Enterprise Inc can provide on-site training for the InfraCal TOG/TPH Analyzers. Topics include instrument operation, calibration, extraction procedures and field sampling. Training can be tailored to a customer's particular requirements. <b>Cost: \$750.00/day plus travel expenses and purchase of appropriate InfraCal Field Sampling Extraction Kits.</b> Contact Wilks Enterprise Inc for more details.

- Master Card, Visa and American Express Cards are accepted

InfraCal and InfraWin are trademarks of Wilks Enterprise Inc.  
Windows is a trademark of Microsoft Corporation